

ME PLC 40 PL S BK - Insertion plate




2202722

<https://www.phoenixcontact.com/us/products/2202722>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 35.3 mm, height: 47.2 mm, depth: 8.4 mm, color: black (similar RAL 9005)



Your advantages

- Tool-free mounting
- Available in 40 mm overall width
- Flammability rating V0 in accordance with UL 94
- Variety of connection technology
- Can be mounted on the DIN rail
- With DIN-rail-mountable bus connector and power connector system as an option

Commercial data

Item number	2202722
Packing unit	10 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHEAZ
GTIN	4055626187730
Weight per piece (including packing)	3.26 g
Weight per piece (excluding packing)	3 g
Country of origin	DE

ME PLC 40 PL S BK - Insertion plate



2202722

<https://www.phoenixcontact.com/us/products/2202722>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME PLC
Product family	ME PLC 40
Ventilation openings present	no

Dimensions

Width	35.3 mm
Height	47.2 mm
Depth	8.4 mm

Material specifications

Color (Insertion plate)	black (RAL 9005)
Material Housing	PC
Flammability rating according to UL 94	V0
CTI according to IEC 60112	225

Mounting

Mounting type	Clip mounting
---------------	---------------

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

ME PLC 40 PL S BK - Insertion plate



2202722

<https://www.phoenixcontact.com/us/products/2202722>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

ME PLC 40 PL S BK - Insertion plate



2202722

<https://www.phoenixcontact.com/us/products/2202722>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com