# UCS CP 7035 - Corner guards

2203346

https://www.phoenixcontact.com/us/products/2203346

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Adapter for protecting the corners of the UCS housing; material: TPE-U; color: light gray, similar to RAL 7035; held in the screw holes of the housing

## Your advantages

- Flexible mounting options for the control cabinet and use in the field
- Can be adapted to suit the application, thanks to identical receptacles in the housing
- Different colors for high recognition value inside and outside the control cabinet

## Commercial data

| | |
|---|---|
| Item number | 2203346 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC03 |
| Product key | ACFCAZ |
| GTIN | 4055626462530 |
| Weight per piece (including packing) | 7.5 g |
| Weight per piece (excluding packing) | 7.4 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

## Technical data

### Notes

| | |
|---|---|
| Assembly note | Please observe the application note in the download area. |

### Product properties

| | |
|---|---|
| Product type | Mounting material |
| Housing type | Universal housings |
| Housing series | UCS |
| Ventilation openings present | no |

### Dimensions

| | |
|---|---|
| Width | 17.3 mm |
| Height | 17.3 mm |
| Depth | 11.7 mm |

### Material specifications

| | |
|---|---|
| Color (Housing) | light gray (RAL 7035) |
| Material | TPE-U |
| Flammability rating according to UL 94 | V2 |
| CTI according to IEC 60112 | 600 |
| Insulating material | TPE-U |

### Environmental and real-life conditions

#### Ambient conditions

| | |
|---|---|
| Max. IP code to attain | IP40 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 95 % |

### Mounting

| | |
|---|---|
| Mounting type | Snap in |

### Packaging specifications

| | |
|---|---|
| Type of packaging | PE bag |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002779 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.103 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com