

HCS-C MEDIUM WIN 2,0 FR128X64S - Washer/ring




2203589

<https://www.phoenixcontact.com/us/products/2203589>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Acrylic glass, satin-finished, frame printed black, for display 128x64



Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

Commercial data

Item number	2203589
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFABZ
GTIN	4055626485317
Weight per piece (including packing)	9.3 g
Weight per piece (excluding packing)	9.3 g
Customs tariff number	39205100
Country of origin	DE

2203589

<https://www.phoenixcontact.com/us/products/2203589>

Technical data

Product properties

Product type	Mounting material
Housing type	Handheld housing
Housing series	HCS

Dimensions

Width	66.8 mm
Height	37.8 mm
Depth	2 mm
Dimensions	60.9 mm x 31.9 mm

Material specifications

Color (Housing)	transparent
Material	PMMA

Environmental and real-life conditions

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	80 °C
Test duration	1 h
Force	20

HCS-C MEDIUM WIN 2,0 FR128X64S - Washer/ring



2203589

<https://www.phoenixcontact.com/us/products/2203589>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HCS-C MEDIUM WIN 2,0 FR128X64S - Washer/ring



2203589

<https://www.phoenixcontact.com/us/products/2203589>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com