

# HCS-T MINI W-GLUE - Adhesive



2203745

<https://www.phoenixcontact.com/us/products/2203745>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Transfer adhesive for display window



## Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

## Commercial data

Item number	2203745
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFABZ
GTIN	4055626485515
Weight per piece (including packing)	4 g
Weight per piece (excluding packing)	4 g
Customs tariff number	39269097
Country of origin	DE

2203745

<https://www.phoenixcontact.com/us/products/2203745>

## Technical data

### Product properties

Product type	Mounting material
Housing type	Handheld housing
Housing series	HCS

### Dimensions

Width	71.6 mm
Depth	0.2 mm
Length	48.8 mm

### Environmental and real-life conditions

#### Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

#### Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	80 °C
Test duration	1 h
Force	20

# HCS-T MINI W-GLUE - Adhesive



2203745

<https://www.phoenixcontact.com/us/products/2203745>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HCS-T MINI W-GLUE - Adhesive



2203745

<https://www.phoenixcontact.com/us/products/2203745>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)