

DCS D-FIX 7,0 - Mounting set

2203830

<https://www.phoenixcontact.com/us/products/2203830>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting set including plate and screws, for display mounting



Your advantages

- Display housing for portable and stationary operating panels
- Integration of TFT display and membrane keypads

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2203830 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC02 |
| Product key | ACFBAZ |
| GTIN | 4055626488851 |
| Weight per piece (including packing) | 63.1 g |
| Weight per piece (excluding packing) | 56.1 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

DCS D-FIX 7,0 - Mounting set

2203830

<https://www.phoenixcontact.com/us/products/2203830>



Technical data

Product properties

| | |
|------------------------------|-------------------|
| Product type | Mounting material |
| Housing type | Display carrier |
| Housing type | Display carriers |
| Housing series | DCS |
| Product family | DCS 7.. |
| Ventilation openings present | no |

Dimensions

| | |
|--------|----------|
| Width | 169.9 mm |
| Depth | 12.5 mm |
| Length | 145.2 mm |

Material specifications

| | |
|-------------------------|-----------|
| Material | Aluminum |
| Surface characteristics | untreated |

DCS D-FIX 7,0 - Mounting set

2203830

<https://www.phoenixcontact.com/us/products/2203830>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

DCS D-FIX 7,0 - Mounting set



2203830

<https://www.phoenixcontact.com/us/products/2203830>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com