

# ME MAX TBUS BS BU - Filler plug



2203933

<https://www.phoenixcontact.com/us/products/2203933>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Filler plugs for TBUS recess, width: 5.8 mm, height: 30 mm, depth: 6.6 mm, color: blue (similar RAL 5015)



## Your advantages

- Easy, tool-free mounting

## Commercial data

Item number	2203933
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHAAZ
GTIN	4055626459431
Weight per piece (including packing)	0.58 g
Weight per piece (excluding packing)	0.58 g
Country of origin	DE

# ME MAX TBUS BS BU - Filler plug



2203933

<https://www.phoenixcontact.com/us/products/2203933>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Ventilation openings present	no

### Dimensions

Width	5.8 mm
Height	30 mm
Depth	6.6 mm

### Material specifications

Color (Filler plug)	blue (RAL 5015)
Material Filler plug	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching
---------------	----------

# ME MAX TBUS BS BU - Filler plug



2203933

<https://www.phoenixcontact.com/us/products/2203933>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2203933>



**UL Recognized**

Approval ID: E240868

# ME MAX TBUS BS BU - Filler plug



2203933

<https://www.phoenixcontact.com/us/products/2203933>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX TBUS BS BU - Filler plug



2203933

<https://www.phoenixcontact.com/us/products/2203933>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)