

# ME MAX B-22,5 RD - Filler plug



2279978

<https://www.phoenixcontact.com/us/products/2279978>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points, width: 20 mm, height: 21.6 mm, depth: 8.1 mm, color: red (similar RAL 3001)

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

Item number	2279978
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	ACHABZ
GTIN	4046356367448
Weight per piece (including packing)	1.1 g
Weight per piece (excluding packing)	1.117 g
Country of origin	DE

# ME MAX B-22,5 RD - Filler plug



2279978

<https://www.phoenixcontact.com/us/products/2279978>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME MAX 22,5..
Ventilation openings present	no

### Dimensions

Width	20 mm
Height	21.6 mm
Depth	8.1 mm

### Material specifications

Color (Filler plug)	red (RAL 3001)
Material Filler plug	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching
---------------	----------

### Packaging specifications

Outer packaging type	Resealable bag
----------------------	----------------

# ME MAX B-22,5 RD - Filler plug

2279978

<https://www.phoenixcontact.com/us/products/2279978>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2279978>



**UL Recognized**

Approval ID: E240868

# ME MAX B-22,5 RD - Filler plug



2279978

<https://www.phoenixcontact.com/us/products/2279978>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX B-22,5 RD - Filler plug



2279978

<https://www.phoenixcontact.com/us/products/2279978>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)