

FLKM 40-PA-MA12/S100 - Front adapter



2287533

<https://www.phoenixcontact.com/us/products/2287533>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Front adapter, for Siemens SIMATIC®- S5-100U I/O card 6ES5 482-8MA13 1 x 32 channels can be connected

Commercial data

Item number	2287533
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK231S
GTIN	4017918056391
Weight per piece (including packing)	103.95 g
Weight per piece (excluding packing)	103.95 g
Customs tariff number	85369010
Country of origin	DE

FLKM 40-PA-MA12/S100 - Front adapter



2287533

<https://www.phoenixcontact.com/us/products/2287533>

Technical data

Product properties

Product type	Front adapter
--------------	---------------

Electrical properties

Max. permissible operating voltage	< 50 V AC
	60 V DC
Max. permissible current	0.5 A (per path)
	4 A (per slip-on connection (0+; 1+; 2+; 3+))

Connection data

Field level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	40
Pitch	2.54 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Standards and regulations

Standards/regulations	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0160 (in parts)

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM 40-PA-MA12/S100 - Front adapter



2287533

<https://www.phoenixcontact.com/us/products/2287533>

Classifications

ECLASS

ECLASS-13.0	27242292
-------------	----------

FLKM 40-PA-MA12/S100 - Front adapter



2287533

<https://www.phoenixcontact.com/us/products/2287533>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com