

FLKM 50-PA-MODI-984 - Front adapter



2290245

<https://www.phoenixcontact.com/us/products/2290245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for Schneider Electric Modicon 984 series 800, analog input/output card (only in conjunction with 50-pos. interface modules)

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2290245 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK231F |
| GTIN | 4017918057930 |
| Weight per piece (including packing) | 273.4 g |
| Weight per piece (excluding packing) | 273.4 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

FLKM 50-PA-MODI-984 - Front adapter



2290245

<https://www.phoenixcontact.com/us/products/2290245>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Front adapter |
|--------------|---------------|

Electrical properties

| | |
|------------------------------------|---|
| Max. permissible operating voltage | 60 V AC/DC |
| Max. permissible current | 1 A (per path) |
| | 8 A (per slip-on connection (0+; 1+; 2+; 3+; B-; B+)) |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
|---------------------------------|------------------|

Standards and regulations

| | |
|-----------------------|-------------------------|
| Standards/regulations | IEC 60664 |
| | IEC 60664A |
| | DIN VDE 0110 |
| | DIN VDE 0160 (in parts) |

Mounting

| | |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

FLKM 50-PA-MODI-984 - Front adapter




2290245

<https://www.phoenixcontact.com/us/products/2290245>

Drawings

Circuit diagram



FLKM 50-PA-MODI-984 - Front adapter



2290245

<https://www.phoenixcontact.com/us/products/2290245>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242292 |
|-------------|----------|

FLKM 50-PA-MODI-984 - Front adapter



2290245

<https://www.phoenixcontact.com/us/products/2290245>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com