


FLKM 50/DO326/S7-300 - Termination board



2321965

<https://www.phoenixcontact.com/us/products/2321965>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE interface module for failsafe 6ES7 326-2BF01-0AB0 module of the SIMATIC® S7-300 (two 50-pos. FLK connectors), module width: 90 mm

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2321965 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK218S |
| GTIN | 4046356428415 |
| Weight per piece (including packing) | 190.5 g |
| Weight per piece (excluding packing) | 173.4 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

Technical data

Product properties

| | |
|-----------------|------------------|
| Product type | Interface module |
| No. of channels | 10 |

Electrical properties

| | |
|------------------------------------|---------|
| Max. permissible operating voltage | 25 V AC |
| | 60 V DC |

Connection data

Field level

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Controller level

| | |
|-----------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of connections | 2 |
| Number of positions | 50 |
| Pitch | 2.54 mm |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Dimensions

Item dimensions

| | |
|--------|---------|
| Width | 89.5 mm |
| Height | 89.6 mm |
| Depth | 65.9 mm |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

FLKM 50/DO326/S7-300 - Termination board

2321965

<https://www.phoenixcontact.com/us/products/2321965>



Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com