

SD FLASH 2GB SOL-PWR-CTR - Program/configuration memory



2400182

<https://www.phoenixcontact.com/us/products/2400182>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB, with license key for an application library for reactive power control (Solarworx).

Similar figure

Your advantages

- License key for application program
- For storing application programs and other files in the file system of the PLC
- Program and configuration memory, plug-in, with license key for function block libraries

Commercial data

Item number	2400182
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRAAZA
GTIN	4046356981835
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	8.5 g
Country of origin	DE

SD FLASH 2GB SOL-PWR-CTR - Program/configuration memory



2400182

<https://www.phoenixcontact.com/us/products/2400182>

Technical data

Product properties

Product type	Storage medium
Application	Reactive power control (Solarworx)
Mounting position	vertical
Memory type	FLASH-EPROM
Memory size	2 GByte

Electrical properties

Maximum power dissipation for nominal condition	0.165 W
---	---------

Supply

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC
Typical current consumption	typ. 50 mA

Material specifications

Housing material	Plastic
------------------	---------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

Mounting

Mounting position	vertical
-------------------	----------

SD FLASH 2GB SOL-PWR-CTR - Program/configuration memory



2400182

<https://www.phoenixcontact.com/us/products/2400182>

Classifications

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

SD FLASH 2GB SOL-PWR-CTR - Program/configuration memory



2400182

<https://www.phoenixcontact.com/us/products/2400182>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com