

POINTS-2500 - Building management system



2404202

<https://www.phoenixcontact.com/us/products/2404202>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Emalytics Controller license for an additional 2500 data points



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2404202 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DR18 |
| Product key | DRHBAA |
| GTIN | 4055626349510 |
| Weight per piece (including packing) | 0.001 MGM |
| Weight per piece (excluding packing) | 0.001 MGM |
| Customs tariff number | 49119900 |
| Country of origin | US |

Technical data

Product properties

| | |
|---------------------|----------------------------|
| Product type | Building management system |
| Area of application | Building technology |

System properties

| | |
|-------------------------------|------------|
| Type of software | Embedded |
| Intended use for the software | Automation |

License information

| | |
|------------------|-----------------|
| Type of license | Runtime license |
| | Upgrade license |
| License duration | not relevant |

Functionality

| | |
|----------------------------------|--------------------|
| Integrated function | Analysis |
| | Data acquisition |
| | Diagnostics |
| | Startup |
| | Communication |
| | Configuration |
| | Project planning |
| | Simulation |
| Target system | Automation station |
| Supported controller | ILC 2050 BI |
| | ILC 2250 BI |
| | Catan C1 EN |
| Number of supported controllers | not relevant |
| Number of data points (Embedded) | 2500 |
| Number of data points (embedded) | 2500 |
| Number of clients | nicht relevant |

System requirements

| | |
|---------------------|---|
| Operating system | Windows® 10 |
| | Windows® 8.1 Enterprise (64-Bit) |
| | Windows® Server 2012 Standard |
| | Windows® Server 2012 R2 Standard |
| Hard disk memory | min. 4 GByte (more recommended depending on the archiving requirements) |
| Interfaces | 1 x Ethernet (10/100 Mbps), RJ45 |
| Languages supported | German, English |
| Screen resolution | 1024 x 768 pixel(s) ,or higher |

POINTS-2500 - Building management system



2404202

<https://www.phoenixcontact.com/us/products/2404202>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242590 |
| ECLASS-15.0 | 27242590 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001435 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43233600 |
|-------------|----------|

POINTS-2500 - Building management system



2404202

<https://www.phoenixcontact.com/us/products/2404202>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com