POINTS-2500 - Building management system

2404202

https://www.phoenixcontact.com/us/products/2404202

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Emalytics Controller license for an additional 2500 data points



powered by niagara framework®

Commercial data

Item number	2404202
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR18
Product key	DRHBAA
GTIN	4055626349510
Weight per piece (including packing)	0.001 MGM
Weight per piece (excluding packing)	0.001 MGM
Customs tariff number	49119900
Country of origin	US

Technical data

Product properties

Product type	Building management system
Area of application	Building technology

System properties

Type of software	Embedded
Intended use for the software	Automation

License information

Type of license	Runtime license
	Upgrade license
License duration	not relevant

Functionality

Integrated function	Analysis
	Data acquisition
	Diagnostics
	Startup
	Communication
	Configuration
	Project planning
	Simulation
Target system	Automation station
Supported controller	ILC 2050 BI
	ILC 2250 BI
	Catan C1 EN
Number of supported controllers	not relevant
Number of data points (Embedded)	2500
Number of data points (embedded)	2500
Number of clients	nicht relevant

System requirements

Operating system	Windows® 10
	Windows® 8.1 Enterprise (64-Bit)
	Windows® Server 2012 Standard
	Windows® Server 2012 R2 Standard
Processor	Intel® Xeon® E5-2640 2.5 GHz (or higher)
Hard disk memory	min. 4 GByte (more recommended depending on the archiving requirements)
Main memory (RAM)	min. 1 GByte
Interfaces	1 x Ethernet (10/100 Mbps), RJ45
Languages supported	German, English
Screen resolution	1024 x 768 pixel(s) ,or higher

Classifications

ECLASS

ECLASS-13.0	27242590
ECLASS-15.0	27242590

ETIM

ETIM 10.0	EC001435

UNSPSC

UNSPSC 21.0	43233600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com