

VISU+ 2 SP IEC 60870 101 - Visualization software



2404841

<https://www.phoenixcontact.com/us/products/2404841>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Driver license for IEC 60870-5-101. Only in conjunction with a valid Visu+ runtime license including driver connection (Visu+ RT-D).

Commercial data

Item number	2404841
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRDADG
GTIN	4055626457505
Weight per piece (including packing)	39.82 g
Weight per piece (excluding packing)	39.82 g
Country of origin	DE

Technical data

Product properties

Product type	Visualization
--------------	---------------

System properties

Intended use for the software	Visualization
-------------------------------	---------------

License information

Type of license	Driver license
-----------------	----------------

Functionality

Basic functions	Connection in accordance with IEC 60870-5-101 via RS-232 or RS-485.
Number of I/O nodes	0

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® XP (SP3)
	Windows® Vista Business
	Windows® 7 Professional SP1 (32-Bit/64-Bit)
	Windows® 7 Ultimate SP1 (32-Bit/64-Bit)
	Windows® 8 Professional (32-Bit/64-Bit)
	Windows® 8 Enterprise (32-Bit/64-Bit)
	Windows® Server 2003
	Windows® Server 2008
	Windows® Server 2008 R2
	Windows® 10 (32-Bit/64-Bit)
Hard disk memory	min. 1 GByte (recommended: 2 GB)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Screen resolution	1024 x 768 pixel(s) (XGA)

2404841

<https://www.phoenixcontact.com/us/products/2404841>

Classifications

ECLASS

ECLASS-13.0

27242502

ETIM

ETIM 9.0

EC001416

UNSPSC

UNSPSC 21.0

43231500

2404841

<https://www.phoenixcontact.com/us/products/2404841>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com