

# PSD-S AS BULB 5W - Incandescent lamp

2700142

<https://www.phoenixcontact.com/us/products/2700142>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bulb, 5 W, 24 V, BA15d base



## Commercial data

Item number	2700142
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL11Z
GTIN	4046356491341
Weight per piece (including packing)	7.9 g
Weight per piece (excluding packing)	7.9 g
Customs tariff number	85392998
Country of origin	CN

# PSD-S AS BULB 5W - Incandescent lamp



2700142

<https://www.phoenixcontact.com/us/products/2700142>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Lamp
Product family	PSD-S
Type	Tube shape
Base	B15d (bayonet)

### Electrical properties

#### General

Input voltage	24 V
Current consumption	typ. 11 mA
Source of light, power	5 W

### Dimensions

Height	42 mm
Diameter	16 mm

### Material specifications

Color	white
Material	Base: BA15d

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

### Mounting

Mounting position	any
-------------------	-----

# PSD-S AS BULB 5W - Incandescent lamp



2700142

<https://www.phoenixcontact.com/us/products/2700142>

## Classifications

### ECLASS

ECLASS-13.0

27110631

### ETIM

ETIM 9.0

EC000399

### UNSPSC

UNSPSC 21.0

32151500

# PSD-S AS BULB 5W - Incandescent lamp



2700142

<https://www.phoenixcontact.com/us/products/2700142>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)