

# UM122-FE KMGY - Foot element



2697466

<https://www.phoenixcontact.com/us/products/2697466>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Base element for the DIN rail, for mounting below UM-PRO PROFILE (width: 122 mm), Foot element



The figure shows a version of the product

## Commercial data

Item number	2697466
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918991210
Weight per piece (including packing)	8.69 g
Weight per piece (excluding packing)	8.69 g
Customs tariff number	39269097
Country of origin	PL

# UM122-FE KMGY - Foot element



2697466

<https://www.phoenixcontact.com/us/products/2697466>

## Technical data

### Product properties

Product type	Base latches
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM122

### Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

# UM122-FE KMGY - Foot element



2697466

<https://www.phoenixcontact.com/us/products/2697466>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2697466>



**UL Recognized**

Approval ID: E240868

# UM122-FE KMGY - Foot element



2697466

<https://www.phoenixcontact.com/us/products/2697466>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM122-FE KMGY - Foot element



2697466

<https://www.phoenixcontact.com/us/products/2697466>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)