

# PSD-S ME B-M - Mounting material

2700164

<https://www.phoenixcontact.com/us/products/2700164>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Foot for tube Ø 25 mm, aluminium, black

## Commercial data

Item number	2700164
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR07
Product key	DRL117
GTIN	4046356491532
Weight per piece (including packing)	109.4 g
Weight per piece (excluding packing)	109.4 g
Customs tariff number	76169990
Country of origin	DE

# PSD-S ME B-M - Mounting material

2700164

<https://www.phoenixcontact.com/us/products/2700164>

## Technical data

### Notes


#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Assembly element
Product family	PSD-S
Scope of supply	1 x terminal block screw (Allen screw) 1 x seal
	1 x terminal block screw (Allen screw) 1 x seal

### Dimensions

Dimensional drawing	
Height	31 mm
Diameter	70 mm

### Material specifications

Color	black (RAL 9005)
Material	Anodized aluminum

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66 (as of item revision 02)
Ambient temperature (operation)	-30 °C ... 60 °C

### Mounting

Mounting type	Screw mounting (Seal enclosed)
Mounting position	any


# PSD-S ME B-M - Mounting material

2700164

<https://www.phoenixcontact.com/us/products/2700164>



## Drawings



# PSD-S ME B-M - Mounting material



2700164

<https://www.phoenixcontact.com/us/products/2700164>

## Classifications

### ECLASS

ECLASS-13.0	27371235
ECLASS-15.0	27371235

### ETIM

ETIM 10.0	EC001154
-----------	----------

### UNSPSC

UNSPSC 21.0	43221500
-------------	----------

# PSD-S ME B-M - Mounting material



2700164

<https://www.phoenixcontact.com/us/products/2700164>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.907 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)