

AX ODP SERVER 150-200UPG - Software dongle



2700420

<https://www.phoenixcontact.com/us/products/2700420>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Upgrade for AX ODP SERVER from 150 to 200 remote control substations.

Please enter the serial number of your end customer's master product. The update/upgrade cannot be released without this data.

Product description

Open Data Port server, communication interface for ODP-compatible visualization with PC Worx-based controllers.

Your advantages

- Data is transmitted either online or as historical values with time stamp, e.g., for OPC-compatible visualizations
- Open communication with supported controllers via GPRS
- Update and upgrade licenses are available

Commercial data

Item number	2700420
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRDADE
GTIN	4046356545747
Weight per piece (including packing)	282.2 g
Weight per piece (excluding packing)	282.2 g
Country of origin	DE

2700420

<https://www.phoenixcontact.com/us/products/2700420>

Technical data

Product properties

Product type	Drivers and interfaces
--------------	------------------------

System properties

Intended use for the software	Driver
-------------------------------	--------

Functionality

Basic functions	The ODP (Open Data Port) server enables the user to communicate openly with supported controllers based on GPRS. Data is transmitted either online or as buffered historical values in the controller with time stamp.
	Upgrade licenses are available
Supported controllers	ILC 1xx
	ILC 3xx
	AXC 1xxx
	AXC 3xxx
	RFC 4xx
Number of I/O nodes	not relevant

System requirements

Operating equipment	Keyboard, mouse
Operating system	MS Windows XP, MS Windows 2003/2008 Server, MS Windows Vista
Processor	Pentium 4/Celeron, 2 GHz
Hard disk memory	2048 Mbyte (recommended: 1 GByte)
Supported browsers	Internet Explorer Version 8 or later
Languages supported	German, English
Optical drive	DVD-ROM
Screen resolution	XGA (1024 x 768)

AX ODP SERVER 150-200UPG - Software dongle



2700420

<https://www.phoenixcontact.com/us/products/2700420>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com