WEBVISIT 6 EXPRESS - Visualization software

2700954

https://www.phoenixcontact.com/us/products/2700954

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



WebVisit 6 is the engineering tool used to create web visualizations for all controllers with integrated web server. The Express version is available free of charge and enables the creation of up to 10 visualization pages as well as linking a maximum of 60 PPO variables.

Your advantages

- Engineering tool used to create web visualizations for all controllers with integrated web server
- The visualization pages are displayed in any standard browser
- No programming knowledge is necessary for the creation of visualization pages

Commercial data

Item number	2700954
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	NULL
Product key	DRDABA
GTIN	4046356661294
Weight per piece (including packing)	32.01 g
Weight per piece (excluding packing)	29.1 g
Customs tariff number	49119900
Country of origin	DE

Technical data

Product properties

Product type	Visualization

System properties

Control system	(Target system) Embedded controller
Type of software	On-premises
Intended use for the software	Web editor

License information

Type of license	Single-user license
	Freeware
Information regarding the type of license	max. 10 visualization pages, max. 60 variables (PPO)

Functionality

Basic functions	The user interface has a functional design and even the basic version offers numerous graphic basic elements and functions.
	The variables needed for visualization are imported directly from PC Worx.
Programming languages supported	HTML5
Control system	(Target system) Embedded controller
Associated hardware	Phoenix Contact control
Number of I/O nodes	128000

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 10 (32-bit/64-bit), as of Build 1511
	Windows®11, as of Build 22000.675
Processor	Intel® Celeron® / Pentium® 1.6 GHz
Hard disk memory	min. 2 GByte
Main memory (RAM)	min. 2 GByte
Supported browsers	Internet Explorer Version 7 or later
	Internet Explorer Version 8 or later
	Internet Explorer Version 10 or later
	Mozilla Firefox Version 44 or later (recommended)
	Google Chrome Version 48 or later (recommended)
	Opera Version 11.64 or later
Languages supported	English
Screen resolution	1024 x 768 pixel(s) (XGA)

Classifications

ECLASS

ECLASS-15.0	27242502

ETIM

ETIM 9.0	EC001416

UNSPSC

UNSPSC 21.0	43231500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com