

FL SNMP OPC AGENT V3 - Driver and interface software



2701136

<https://www.phoenixcontact.com/us/products/2701136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SNMP-OPC agent, German and English, for integrating OPC-based automation solutions in company-wide network management systems

Your advantages

- Freely configurable alarm conditions
- Any number of SNMP trap receivers can be configured

Commercial data

Item number	2701136
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN21
Product key	DNN155
GTIN	4046356712927
Weight per piece (including packing)	255.555 g
Weight per piece (excluding packing)	255.555 g
Customs tariff number	85234910
Country of origin	DE

FL SNMP OPC AGENT V3 - Driver and interface software



2701136

<https://www.phoenixcontact.com/us/products/2701136>

Technical data

Product properties

Product type	Drivers and interfaces
Scope of supply	CD-ROM with German and English product version and online documentation

System properties

Intended use for the software	Configuration
	Diagnostics

Functionality

Basic functions	Monitoring of OPC server, access to OPC server, SNMP proxy agent, SNMP Version v1 and v2c supported
	Network monitoring with HMI/SCADA systems
Expanded functionality	The SNMP OPC agent V3 is designed for a maximum of 100 data points. If additional devices are required, an extension license (Item No. 2700135) is available.
Associated hardware	Ethernet infrastructure components
Number of I/O nodes	not relevant

System requirements

Operating equipment	Keyboard, mouse recommended
Operating system	Windows XP SP3
	Windows 7
	Windows® Server 2008
	Windows® Server 2003
	Windows® Vista Business
Processor	PC Pentium > 266 MHz
Hard disk memory	min. 20 Mbyte
Languages supported	German, English
Optical drive	CD-ROM

FL SNMP OPC AGENT V3 - Driver and interface software



2701136

<https://www.phoenixcontact.com/us/products/2701136>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com