

CF FLASH 2GB - Memory

2701185

<https://www.phoenixcontact.com/us/products/2701185>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Program and configuration memory, plug-in, 2 Gbytes.



Product description

Program and configuration memory to save the application programs and other files in the file system of the PLC. Alternatively, a program and configuration memory with integrated license is available to disconnect various function blocks.

Your advantages

- For storing application programs and other files in the file system of the PLC
- Program and configuration memory, plug-in

Commercial data

Item number	2701185
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR10
Product key	DRAAZA
GTIN	4046356717144
Weight per piece (including packing)	17.133 g
Weight per piece (excluding packing)	15 g
Customs tariff number	85235110
Country of origin	TW

CF FLASH 2GB - Memory

2701185

<https://www.phoenixcontact.com/us/products/2701185>



Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Storage medium
Application	Program/configuration memory
Memory type	FLASH-EPROM
Memory size	2 GByte

Electrical properties

Maximum power dissipation for nominal condition	0.4 W
---	-------

Supply

Supply voltage	3.3 V DC
Supply voltage range	3.135 V DC ... 3.465 V DC
Typical current consumption	typ. 120 mA

Dimensions

Width	36.4 mm
Height	42.8 mm
Depth	3.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

CF FLASH 2GB - Memory

2701185

<https://www.phoenixcontact.com/us/products/2701185>



Classifications

ECLASS

ECLASS-13.0	27242212
ECLASS-15.0	27242212

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

CF FLASH 2GB - Memory



2701185

<https://www.phoenixcontact.com/us/products/2701185>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	4.942 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com