

# SD FLASH 2GB EMWISE EXTENDED - Program/configuration memory



2701747

<https://www.phoenixcontact.com/us/products/2701747>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB, with license key and EMWISE EXTENDED application program, for use with an ILC 191 ME/AN Inline controller.

This item is replaced by SD FLASH 2GB EMLOG (2403484).

## Product description

Program and configuration memory with EMWISE EXTENDED application program

- Complete configuration and startup via integrated web interface
- 24 pulse inputs, maximum
- 8 analog inputs, maximum
- Connection of a maximum of 10 EMpro devices
- Connection of a maximum of 10 IB IL PM 3P/N/EF-PAC Inline power measurement terminals
- Forwarding of data to a management system via SQL server, OPC, Modbus/TCP, and CSV file

## Your advantages

- Max. 24 pulse inputs (with IB IL 24 DI8/HD-PAC)
- Max. 10 power measurement terminals (IB IL PM 3P/N/EF-PAC)
- Program and configuration memory, plug-in, with license key and application program for reading from measuring devices
- License key for application program
- Max. 8 analog inputs (with IB IL AI 2/SF-PAC)
- Max. 10 EMpro EEM-MA250/400/600 energy measuring devices
- Forwarding of data to a management system via SQL server, OPC, Modbus/TCP, and CSV file
- Complete configuration and startup via integrated web interface
- For storing application programs and other files in the file system of the PLC
- Required item: ILC 191 ME/AN, Order No. 2700074

## Commercial data

Item number	2701747
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR10
Product key	DRAAZA
GTIN	4046356809221
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	8.5 g

# SD FLASH 2GB EMWISE EXTENDED - Program/configuration memory



2701747

<https://www.phoenixcontact.com/us/products/2701747>

Customs tariff number	85235190
Country of origin	DE

# SD FLASH 2GB EMWISE EXTENDED - Program/configuration memory



2701747

<https://www.phoenixcontact.com/us/products/2701747>

## Technical data

### Notes

Order information:	This item is replaced by SD FLASH 2GB EMLOG (2403484).
--------------------	--

### Product properties

Product type	Storage medium
Application	Reading of measuring devices
Mounting position	vertical
Memory type	FLASH-EPROM
Memory size	2 GByte

### Electrical properties

Maximum power dissipation for nominal condition	0.165 W
---	---------

### Supply

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC
Typical current consumption	typ. 50 mA

### Material specifications

Housing material	Plastic
------------------	---------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

### Mounting

Mounting position	vertical
-------------------	----------

# SD FLASH 2GB EMWISE EXTENDED - Program/configuration memory



2701747

<https://www.phoenixcontact.com/us/products/2701747>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)