

PLD E 608-CA-MS/0,6/FS AM - Power cable



2702303

<https://www.phoenixcontact.com/us/products/2702303>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Power cable, 3-position, PVC, orange RAL 2004, cable length: 0.6 m



Product description

The cable serves to connect multiple 600 class PLD enclosure lights in series.

Commercial data

Item number	2702303
Packing unit	1 pc
Sales key	DR08
Product key	DRL23Z
GTIN	4055626112282
Weight per piece (including packing)	95.2 g
Weight per piece (excluding packing)	95.2 g
Customs tariff number	85444290
Country of origin	DE

2702303

<https://www.phoenixcontact.com/us/products/2702303>

Technical data

Product properties

Product type	Power cable
Application	Enclosure lights
Number of positions	3
No. of cable outlets	1
Shielded	no

Material specifications

Material for screw connection	not available
Outer sheath, material	PVC
Conductor material	Bare Cu litz wires

Electrical properties

Nominal voltage U_N	250 V AC
Nominal current I_N	16 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

Connector

Connection 1

Head design	Plug
Head cable outlet	straight
Coding	black

Connection 2

Head design	Socket
Head cable outlet	straight

Cable/line

Cable length	0.6 m
--------------	-------

H05VV-F3G [PVC]

Number of positions	3
Shielded	no
Cable type	H05VV-F3G [PVC]
AWG signal line	16
Wire diameter incl. insulation	2.7 mm
External cable diameter	7.8 mm
Outer sheath, material	PVC
External sheath, color	orange RAL 2004

PLD E 608-CA-MS/0,6/FS AM - Power cable



2702303

<https://www.phoenixcontact.com/us/products/2702303>

Conductor material	Bare Cu litz wires
Material wire insulation	PVC TI2
Smallest bending radius, fixed installation	40 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP40 (plugged in)
Ambient temperature (operation)	-5 °C ... 40 °C

PLD E 608-CA-MS/0,6/FS AM - Power cable



2702303

<https://www.phoenixcontact.com/us/products/2702303>

Classifications

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

2702303

<https://www.phoenixcontact.com/us/products/2702303>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com