

# UEGM-SE 5-SO1-LS GN - Housing half shell



2706386

<https://www.phoenixcontact.com/us/products/2706386>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Lateral element, color: green (similar RAL 6021)

## Commercial data

Item number	2706386
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ACHCCB
GTIN	4017918617097
Weight per piece (including packing)	18.21 g
Weight per piece (excluding packing)	13.75 g
Customs tariff number	85369010
Country of origin	DE

# UEGM-SE 5-SO1-LS GN - Housing half shell



2706386

<https://www.phoenixcontact.com/us/products/2706386>

## Technical data

### Product properties

Product type	Housing half shells
Housing type	Component housing
Housing series	UEG
Product family	UEGM
Ventilation openings present	yes

### Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing material	PA

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

# UEGM-SE 5-SO1-LS GN - Housing half shell



2706386

<https://www.phoenixcontact.com/us/products/2706386>

## Classifications

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEGM-SE 5-SO1-LS GN - Housing half shell



2706386

<https://www.phoenixcontact.com/us/products/2706386>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)