FL NETWORK MANAGER BASIC - Software

2702889

https://www.phoenixcontact.com/us/products/2702889

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRA-READY



Software; Single-user license; application: Network configuration; Associated hardware: Ethernet infrastructure components; Type of software: On-premises; Basic functions: Network commissioning, Network configuration, Firmware update

Your advantages

- All required services, such as BootP and TFTP server, included
- Rapid network startup thanks to multi-device configuration
- Also suitable for PROFINET switches, thanks to DCP support
- Non-proprietary use also possible, thanks to SNMP and FDCML standard
- Special support for Phoenix Contact Factoryline devices

Commercial data

Item number	2702889
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN21
Product key	DNN155
GTIN	4055626379463
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	0.001 g
Customs tariff number	85234920
Country of origin	DE

Technical data

Notes

Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Product properties

Product type	Network management software

System properties

Type of software	On-premises
Intended use for the software	Network configuration

License information

Type of license	Single-user license

Functionality

Basic functions	Network commissioning
	Network configuration
	Firmware update
	Network representation
	IP assignment via BootP, DHCP, DCP
	Handling of configuration files
	Multi-device configuration
	SNMP scripting
	VLAN configuration assistant
	Offline configuration
Expanded functionality	The FL Network Manager is not limited to a maximum number of nodes
Associated hardware	Ethernet infrastructure components

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 10 (64 bit) from version 20H2, Windows® 11 from version 21H2
Note about the operating system	.NET Framework 4.8 required
Processor	Intel® Core™ i5
Hard disk memory	min. 1 GByte
Main memory (RAM)	8 GByte
Network card	Correctly configured ETHERNET network card with TCP/IP protocol stack
Interfaces	Ethernet Port
Languages supported	German, English

Classifications

ECLASS

ECLASS-13.0	19240201
ECLASS-15.0	19240201

ETIM

ETIM 10.0	EC000501

UNSPSC

UNSPSC 21.0	43232900

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com