

FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SNMP-based software for easy commissioning and monitoring of network components such as switches, routers, and WLAN access points

Your advantages

- All required services, such as BootP and TFTP server, included
- Rapid network startup thanks to multi-device configuration
- Also suitable for PROFINET switches, thanks to DCP support
- Non-proprietary use also possible, thanks to SNMP and FDCML standard
- Special support for Phoenix Contact Factoryline devices

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2702889 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN21 |
| Product key | DNN155 |
| GTIN | 4055626379463 |
| Weight per piece (excluding packing) | 0.001 g |
| Customs tariff number | 85234920 |
| Country of origin | DE |

FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

Technical data

Product properties

| | |
|--------------|-----------------------------|
| Product type | Network management software |
|--------------|-----------------------------|

System properties

| | |
|-------------------------------|-----------------------|
| Type of software | On-premises |
| Intended use for the software | Network configuration |

License information

| | |
|-----------------|---------------------|
| Type of license | Single-user license |
|-----------------|---------------------|

Functionality

| | |
|------------------------|--|
| Basic functions | Network configuration |
| | Firmware update |
| | IP assignment via BootP, DHCP, DCP |
| | Handling of configuration files |
| | Multi-device configuration |
| | SNMP scripting |
| | Network representation |
| | VLAN configuration assistant |
| Offline configuration | |
| Expanded functionality | The FL Network Manager is not limited to a maximum number of nodes |
| Associated hardware | Ethernet infrastructure components |

System requirements

| | |
|---------------------------------|---|
| Operating equipment | Keyboard, mouse |
| Operating system | Windows® 10 (64 bit) from version 20H2, Windows® 11 from version 21H2 |
| Note about the operating system | .NET Framework 4.8 required |
| Hard disk memory | min. 1 GByte |
| Network card | Correctly configured ETHERNET network card with TCP/IP protocol stack |
| Interfaces | Ethernet Port |
| Languages supported | German, English |

FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19240201 |
| ECLASS-15.0 | 19240201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000501 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43232900 |
|-------------|----------|

FL NETWORK MANAGER BASIC - Network management software



2702889

<https://www.phoenixcontact.com/us/products/2702889>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com