

ME DH27 NS 35 LBGY - Spacer




2707563

<https://www.phoenixcontact.com/us/products/2707563>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer, for protecting the input and output contacts for NS 35 DIN rails



Your advantages

- Easy installation

Commercial data

Item number	2707563
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHACZ
GTIN	4017918902629
Weight per piece (including packing)	11.4 g
Weight per piece (excluding packing)	11.32 g
Country of origin	DE

ME DH27 NS 35 LBGY - Spacer



2707563

<https://www.phoenixcontact.com/us/products/2707563>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Mounting material
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

Dimensions

Width	30.5 mm
Height	88 mm
Depth	22.8 mm

Material specifications

Color (Housing)	beige (RAL 7032)
Material Housing	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

ME DH27 NS 35 LBGY - Spacer



2707563

<https://www.phoenixcontact.com/us/products/2707563>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2707563>



UL Recognized

Approval ID: E240868

ME DH27 NS 35 LBGY - Spacer



2707563

<https://www.phoenixcontact.com/us/products/2707563>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME DH27 NS 35 LBGY - Spacer



2707563

<https://www.phoenixcontact.com/us/products/2707563>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.106 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com