

# ME B-SA/NS 35 GNTQ - Cover



2709600

<https://www.phoenixcontact.com/us/products/2709600>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal cover, 1 strip covers up to 12 terminal points, for ME-BUS male side, (female side)



## Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

## Commercial data

Item number	2709600
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHACZ
GTIN	4017918884086
Weight per piece (including packing)	300 g
Weight per piece (excluding packing)	299.9 g
Country of origin	DE

2709600

<https://www.phoenixcontact.com/us/products/2709600>

## Technical data

### Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

### Dimensions

Width	14.5 mm
Height	91.1 mm
Depth	17.9 mm
Depth from top edge of DIN rail	15.2 mm

### Material specifications

Color (Filler plug)	turquoise green (RAL 5018)
Material Filler plug	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
------------------------	------

### Mounting

Mounting type	Snap in
---------------	---------

# ME B-SA/NS 35 GNTQ - Cover



2709600

<https://www.phoenixcontact.com/us/products/2709600>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2709600>



**UL Recognized**

Approval ID: E240868

# ME B-SA/NS 35 GNTQ - Cover



2709600

<https://www.phoenixcontact.com/us/products/2709600>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME B-SA/NS 35 GNTQ - Cover



2709600

<https://www.phoenixcontact.com/us/products/2709600>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)