

IB IL SCN-12-OCP - Inline connector



2727624

<https://www.phoenixcontact.com/us/products/2727624>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline connector; green (RAL 6021); type: 12 terminal points (color-coded); Terminal point numbering: 1.1, 2.1 ... 1.6, 2.6; scope: Inline digital output terminal

Commercial data

Item number	2727624
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	DR01
Product key	DRI1Z1
GTIN	4017918168193
Weight per piece (including packing)	22.19 g
Weight per piece (excluding packing)	22.19 g
Customs tariff number	85366990
Country of origin	DE

IB IL SCN-12-OCP - Inline connector



2727624

<https://www.phoenixcontact.com/us/products/2727624>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Plug
Area of application	Inline digital output terminal

Connection data

Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Dimensions

Width	12 mm
Height	136.2 mm
Depth	41 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Characteristics

Design,	12 terminal points
---------	--------------------

IB IL SCN-12-OCP - Inline connector



2727624

<https://www.phoenixcontact.com/us/products/2727624>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2727624>



cULus Recognized
Approval ID: E140324

IB IL SCN-12-OCP - Inline connector



2727624

<https://www.phoenixcontact.com/us/products/2727624>

Classifications

ECLASS

ECLASS-13.0	27242692
ECLASS-15.0	27242692

ETIM

ETIM 10.0	EC002584
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB IL SCN-12-OCP - Inline connector



2727624

<https://www.phoenixcontact.com/us/products/2727624>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.632 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com