

# PC WORX 3 DEMO - License



2730967

<https://www.phoenixcontact.com/us/products/2730967>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PC Worx 3 Demo, software package with Quick-start manual in all the available languages. Only 8 bytes of output data/8 bytes of input data can be used if no additional license has been procured (e.g. 16 digital I/Os)

## Your advantages

- Integrated simulation environment
- Comprehensive diagnostic possibilities such as breakpoints, individual steps, debugging in libraries, instance debugging
- Fast startup and programming, thanks to comprehensive standard libraries
- Uniform operation worldwide, thanks to programming according to IEC 61131
- A programming environment for all controllers from Phoenix Contact
- Integrated diagnostics and monitoring
- Integrated fieldbus and network configuration
- Application-specific expansion with corresponding functional blocks

## Commercial data

Item number	2730967
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRDBAC
GTIN	4017918904517
Weight per piece (including packing)	250 g
Weight per piece (excluding packing)	250 g
Customs tariff number	85234945
Country of origin	DE

## Technical data

### Product properties

Product type	License
Scope of supply	Software package contains: Software on CD, manual (Quick Start), registration

### System properties

Control system	(Target system) Field controllers, Remote Field Controllers
Intended use for the software	Programming

### Functionality

Basic functions	Planning an automation system, parameterizing the INTERBUS and PROFINET devices, operating INTERBUS and PROFINET, programming an automation system in acc. with IEC 61131-3. communication in acc. with IEC 61131-5	
	Symbolic flowchart (SFC)	
	Instruction list (IL)	
	Structured text (ST)	
	Ladder diagram (LD)	
	Network configuration (functionality of Config+)	
	Network diagnostics (functionality of Diag+)	
Expanded functionality	16 byte input and output data (demo version)	
Integrated function	Analysis	
	Evaluation	
	Data acquisition	
	Programming	
	Configuration	
	Diagnostics	
	Maintenance	
Programming languages supported	Communication	
	Programming in acc. with IEC 61131-3	
	Instruction list (IL)	
	Function block diagram (FBD)	
	Ladder diagram (LD)	
Configuration	Structured text (ST)	
	Symbolic flowchart (SFC)	
	INTERBUS	
	Diagnostics	INTERBUS
	Control system	(Target system) Field controllers, Remote Field Controllers
Associated hardware	Phoenix Contact control	

### System requirements

Operating equipment	Keyboard, mouse
Processor	Pentium III or higher

# PC WORX 3 DEMO - License



2730967

<https://www.phoenixcontact.com/us/products/2730967>

Hard disk memory	249.99561309814 Mbyte
Optical drive	CD-ROM
Screen resolution	800 x 600

# PC WORX 3 DEMO - License



2730967

<https://www.phoenixcontact.com/us/products/2730967>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)