

PC WORX 3 PRO LIC - License



2730983

<https://www.phoenixcontact.com/us/products/2730983>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PC-WORX 3 Pro licence with unlimited number of I/O nodes (within the system limits specified in the data sheet), does not include MSFC licence.

Your advantages

- Comprehensive diagnostic possibilities such as breakpoints, individual steps, debugging in libraries, instance debugging
- Integrated simulation environment
- Fast startup and programming, thanks to comprehensive standard libraries
- Uniform operation worldwide, thanks to programming according to IEC 61131
- A programming environment for all controllers from Phoenix Contact
- Integrated diagnostics and monitoring
- Application-specific expansion with corresponding functional blocks
- Integrated fieldbus and network configuration

Commercial data

Item number	2730983
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRDBAC
GTIN	4017918904524
Weight per piece (including packing)	290 g
Weight per piece (excluding packing)	165 g
Customs tariff number	85234910
Country of origin	DE

2730983

<https://www.phoenixcontact.com/us/products/2730983>

Technical data

Product properties

Product type	License
--------------	---------

System properties

Control system	(Target system) Field controllers, Remote Field Controllers
Intended use for the software	License programming

Functionality

Basic functions	Function block diagram (FBD)
	Instruction list (IL)
	Structured text (ST)
	Ladder diagram (LD)
	Symbolic flowchart (SFC)
	Configuration of INTERBUS networks
	Parameterizing the INTERBUS devices
	Diagnostics for INTERBUS networks
Expanded functionality	Unlimited number of input/output data
	Machine Sequential Function Chart (MSFC)
Integrated function	Analysis
	Evaluation
	Data acquisition
	Programming
	Configuration
	Diagnostics
	Maintenance
	Communication
Programming languages supported	Programming in acc. with IEC 61131-3
	Instruction list (IL)
	Function block diagram (FBD)
	Ladder diagram (LD)
	Structured text (ST)
	Symbolic flowchart (SFC)
Configuration	INTERBUS
Diagnostics	INTERBUS
Control system	(Target system) Field controllers, Remote Field Controllers
Associated hardware	Phoenix Contact control
Supported controller	Field controllers and Remote Field Controllers

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows NT 4.0 (SP6), Windows 2000, Windows XP
Processor	Pentium > 800 MHz

PC WORX 3 PRO LIC - License



2730983

<https://www.phoenixcontact.com/us/products/2730983>

Hard disk memory	250 Mbyte
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Spanish
Administrator rights required for installation	yes
Optical drive	CD-ROM
Screen resolution	800x600

PC WORX 3 PRO LIC - License



2730983

<https://www.phoenixcontact.com/us/products/2730983>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
-----------------------------------------	-------------------------------------------------------------------------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com