

# ME DH27 NS 35 BUGY - Spacer



2735535

<https://www.phoenixcontact.com/us/products/2735535>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer, for protecting the input and output contacts for NS 35 DIN rails



## Your advantages

- Easy installation

## Commercial data

Item number	2735535
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHACZ
GTIN	4017918591984
Weight per piece (including packing)	11.144 g
Weight per piece (excluding packing)	9.338 g
Country of origin	DE

# ME DH27 NS 35 BUGY - Spacer



2735535

<https://www.phoenixcontact.com/us/products/2735535>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Mounting material
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

### Dimensions

Width	30.5 mm
Height	88 mm
Depth	22.8 mm

### Material specifications

Color (Housing)	blue gray (RAL 7031)
Material Housing	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

# ME DH27 NS 35 BUGY - Spacer



2735535

<https://www.phoenixcontact.com/us/products/2735535>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2735535>



**UL Recognized**

Approval ID: E240868

# ME DH27 NS 35 BUGY - Spacer



2735535

<https://www.phoenixcontact.com/us/products/2735535>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME DH27 NS 35 BUGY - Spacer



2735535

<https://www.phoenixcontact.com/us/products/2735535>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)