

FL CAT5 HEAVY - Data cable



2744814

<https://www.phoenixcontact.com/us/products/2744814>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CAT5-SF/UTP cable (J-02YS(ST)C HP 2 x 2 x 24 AWG), heavy-duty installation cable, 2 x 2 x 0.22 mm², solid conductor, shielded, outer sheath: 7.8 mm diameter, inner sheath: 5.75 mm ± 0.15 mm diameter

Commercial data

Item number	2744814
Packing unit	1 m
Minimum order quantity	1 m
Note	Made to order (non-returnable)
Sales key	BF04
Product key	AF1LEA
GTIN	4017918600518
Weight per piece (including packing)	66.72 g
Weight per piece (excluding packing)	45 g
Customs tariff number	85444993
Country of origin	DE

FL CAT5 HEAVY - Data cable



2744814

<https://www.phoenixcontact.com/us/products/2744814>

Technical data

Product properties

Product type	Data cable by the meter
Number of positions	4
Shielded	yes

Electrical properties

Nominal voltage U_N	48 V AC
Transmission medium	Copper
Transmission speed	100 Mbps

Interfaces

Signal type/category	Ethernet CAT5 (IEC 11801), 100 Mbps
----------------------	-------------------------------------

Cable/line

Cable length	Free input (0.25 ... 1000.0 m)
External sheath, color	blue

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation)	-5 °C ... 60 °C (Cable, flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C

FL CAT5 HEAVY - Data cable



2744814

<https://www.phoenixcontact.com/us/products/2744814>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2744814>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00395

FL CAT5 HEAVY - Data cable



2744814

<https://www.phoenixcontact.com/us/products/2744814>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FL CAT5 HEAVY - Data cable



2744814

<https://www.phoenixcontact.com/us/products/2744814>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.214 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com