

# UEGM-SE 5 BK - Housing half shell



2757568

<https://www.phoenixcontact.com/us/products/2757568>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element for electronic housing UEGM ...

## Commercial data

Item number	2757568
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC11
Product key	ACHCCB
GTIN	4017918244736
Weight per piece (including packing)	17.62 g
Weight per piece (excluding packing)	17.62 g
Customs tariff number	85472000
Country of origin	DE

# UEGM-SE 5 BK - Housing half shell



2757568

<https://www.phoenixcontact.com/us/products/2757568>

## Technical data

### Product properties

Product type	Housing half shells
Housing type	Component housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM
Ventilation openings present	yes

### Material specifications

Color (Housing)	black (RAL 9005)
Material	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

### Mounting

Mounting type	Snap in
---------------	---------

# UEGM-SE 5 BK - Housing half shell



2757568

<https://www.phoenixcontact.com/us/products/2757568>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2757568>



**UL Recognized**

Approval ID: E240868

# UEGM-SE 5 BK - Housing half shell



2757568

<https://www.phoenixcontact.com/us/products/2757568>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEGM-SE 5 BK - Housing half shell



2757568

<https://www.phoenixcontact.com/us/products/2757568>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)