

# UEGM 27,5-SMD - Electronics housing



2757063

<https://www.phoenixcontact.com/us/products/2757063>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic housing, for PCB insertion, fully equipped with 3 screw connections per side, for mounting of SMD components

The figure shows version UEGM 22.5

## Commercial data

Item number	2757063
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCCB
GTIN	4017918139537
Weight per piece (including packing)	57.75 g
Weight per piece (excluding packing)	57.75 g
Customs tariff number	85369010
Country of origin	DE

## Technical data

### Product properties

Product type	Complete housing
Housing type	Component housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM 27,5
Type	Connection system integrated, housing closed
Number of positions	6
Pitch	5 mm
Number of rows	1
Ventilation openings present	no
Pin layout	Linear pinning


### Electrical properties

Nominal voltage $U_N$	500 V (Voltage and current values are affected by the configuration of the printed circuit board.)
Nominal current $I_N$	10 A

### Connection data

Connection method	Screw connection
-------------------	------------------

### Dimensions

Dimensional drawing	
Width	27.5 mm
Installed height	85.5 mm
Height NS 35/7,5	85.5 mm
Depth	79 mm
Length	79 mm
Pitch	5 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA
Flammability rating according to UL 94	V2

### Environmental and real-life conditions

# UEGM 27,5-SMD - Electronics housing



2757063

<https://www.phoenixcontact.com/us/products/2757063>

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

## Mounting

Mounting type	DIN rail mounting
Pin layout	Linear pinning

# UEGM 27,5-SMD - Electronics housing


2757063

<https://www.phoenixcontact.com/us/products/2757063>



## Drawings

Dimensional drawing




# UEGM 27,5-SMD - Electronics housing

2757063

<https://www.phoenixcontact.com/us/products/2757063>

Dimensional drawing



UEGM 25... und UEGM 27,5-SMD with 1 PCB, 6 positions or 12 positions (FS/FS)

Dimensional drawing




# UEGM 27,5-SMD - Electronics housing

2757063


<https://www.phoenixcontact.com/us/products/2757063>



Exploded view



Schematic diagram



# UEGM 27,5-SMD - Electronics housing



2757063

<https://www.phoenixcontact.com/us/products/2757063>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2757063>



**UL Recognized**

Approval ID: E240868

# UEGM 27,5-SMD - Electronics housing



2757063

<https://www.phoenixcontact.com/us/products/2757063>

## Classifications

### ECLASS

ECLASS-13.0	27190501
ECLASS-15.0	27190501

### ETIM

ETIM 10.0	EC001031
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEGM 27,5-SMD - Electronics housing



2757063

<https://www.phoenixcontact.com/us/products/2757063>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)