

UEG 20 KMGY SO32 - Electronics housing



2757283

<https://www.phoenixcontact.com/us/products/2757283>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronics housing, color: light gray ,Component housing

Commercial data

Item number	2757283
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	ACHCCA
GTIN	4017918367725
Weight per piece (including packing)	47.346 g
Weight per piece (excluding packing)	47.346 g
Country of origin	DE

2757283

<https://www.phoenixcontact.com/us/products/2757283>

Technical data

Product properties

Product type	Complete housing
Housing type	Component housing
Housing series	UEG
Product family	UEG

Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

UEG 20 KMGY SO32 - Electronics housing




2757283

<https://www.phoenixcontact.com/us/products/2757283>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2757283>

 cULus Recognized Approval ID: E60425-19770427		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B		300 V	10 A	30 - 12	-
D		300 V	10 A	30 - 12	-

UEG 20 KMGY SO32 - Electronics housing



2757283

<https://www.phoenixcontact.com/us/products/2757283>

Classifications

ECLASS

ECLASS-13.0	27190101
ECLASS-15.0	27190101

ETIM

ETIM 10.0	EC001031
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UEG 20 KMGY SO32 - Electronics housing



2757283

<https://www.phoenixcontact.com/us/products/2757283>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com