

# UEG-FE BK (VPE100) - Base latch



2757584

<https://www.phoenixcontact.com/us/products/2757584>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Base latch, width: 12 mm, height: 61.25 mm, depth: 16.1 mm, color: black (similar RAL 9005)

## Commercial data

Item number	2757584
Packing unit	100 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	AC11
Product key	ACHCCA
GTIN	4017918244750
Weight per piece (including packing)	5.12 g
Weight per piece (excluding packing)	4.46 g
Customs tariff number	85369010
Country of origin	DE

# UEG-FE BK (VPE100) - Base latch



2757584

<https://www.phoenixcontact.com/us/products/2757584>

## Technical data

### Product properties

Product type	Base latches
Housing type	Component housing
Housing series	UEG
Product family	UEG

### Dimensions

Width	12 mm
Height	61.25 mm
Depth	16.1 mm

### Material specifications

Color (Housing)	black (RAL 9005)
Material Housing	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

# UEG-FE BK (VPE100) - Base latch



2757584

<https://www.phoenixcontact.com/us/products/2757584>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2757584>



**UL Recognized**

Approval ID: E240868

# UEG-FE BK (VPE100) - Base latch



2757584

<https://www.phoenixcontact.com/us/products/2757584>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEG-FE BK (VPE100) - Base latch



2757584

<https://www.phoenixcontact.com/us/products/2757584>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)