

ATP-UKK 3/5 - Partition plate



2778521

<https://www.phoenixcontact.com/us/products/2778521>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Partition plate, depth: 56 mm, width: 2.5 mm, height: 64 mm, color: gray



Commercial data

Item number	2778521
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
GTIN	4017918068721
Weight per piece (including packing)	5.714 g
Weight per piece (excluding packing)	5.3 g
Customs tariff number	39269097
Country of origin	DE

ATP-UKK 3/5 - Partition plate



2778521

<https://www.phoenixcontact.com/us/products/2778521>

Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Dimensions

Width	2.5 mm
Height	64 mm
Depth	56 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

ATP-UKK 3/5 - Partition plate



2778521

<https://www.phoenixcontact.com/us/products/2778521>

Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 10.0	EC000886
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

ATP-UKK 3/5 - Partition plate



2778521

<https://www.phoenixcontact.com/us/products/2778521>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com