

# UEG-FE - Base latch

2790318

<https://www.phoenixcontact.com/us/products/2790318>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Base latch, width: 12 mm, height: 61.25 mm, depth: 16.1 mm, color: green (similar RAL 6021)

## Commercial data

Item number	2790318
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCCA
GTIN	4017918118402
Weight per piece (including packing)	5.49 g
Weight per piece (excluding packing)	5.49 g
Customs tariff number	85369010
Country of origin	DE

## Technical data

### Product properties

Product type	Base latches
Housing type	Component housing
Housing series	UEG
Product family	UEG

### Dimensions

Width	12 mm
Height	61.25 mm
Depth	16.1 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

# UEG-FE - Base latch

2790318

<https://www.phoenixcontact.com/us/products/2790318>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2790318>



**UL Recognized**

Approval ID: E240868

# UEG-FE - Base latch

2790318

<https://www.phoenixcontact.com/us/products/2790318>



## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEG-FE - Base latch



2790318

<https://www.phoenixcontact.com/us/products/2790318>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)