

UEG-FE - Base latch

2790318

<https://www.phoenixcontact.com/us/products/2790318>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Base latch, width: 12 mm, height: 61.25 mm, depth: 16.1 mm, color: green (similar RAL 6021)

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2790318 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC11 |
| Product key | ACHCCA |
| GTIN | 4017918118402 |
| Weight per piece (including packing) | 5.49 g |
| Weight per piece (excluding packing) | 5.49 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

Technical data

Product properties

| | |
|----------------|-------------------|
| Product type | Base latches |
| Housing type | Component housing |
| Housing series | UEG |
| Product family | UEG |

Dimensions

| | |
|--------|----------|
| Width | 12 mm |
| Height | 61.25 mm |
| Depth | 16.1 mm |

Material specifications

| | |
|--|------------------|
| Color (Housing) | green (RAL 6021) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

UEG-FE - Base latch

2790318

<https://www.phoenixcontact.com/us/products/2790318>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2790318>



UL Recognized

Approval ID: E240868

UEG-FE - Base latch

2790318

<https://www.phoenixcontact.com/us/products/2790318>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UEG-FE - Base latch



2790318

<https://www.phoenixcontact.com/us/products/2790318>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.036 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com