

# UEGM/H-FE - Intermediate element



2792060

<https://www.phoenixcontact.com/us/products/2792060>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic housing, Intermediate element with base latch, without vents, width: 27.3 mm, height: 79.2 mm, depth: 66.3 mm, color: green (similar RAL 6021), cross connection: Not provided for

## Commercial data

Item number	2792060
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC11
Product key	ACHCCB
GTIN	4017918349424
Weight per piece (including packing)	14.82 g
Weight per piece (excluding packing)	14.82 g
Customs tariff number	85369010
Country of origin	DE

# UEGM/H-FE - Intermediate element



2792060

<https://www.phoenixcontact.com/us/products/2792060>

## Technical data

### Product properties

Product type	Component housing center part
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM
Ventilation openings present	no

### Dimensions

Width	27.3 mm
Height	79.2 mm
Depth	66.3 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching with housing half-shell
---------------	----------------------------------

# UEGM/H-FE - Intermediate element



2792060

<https://www.phoenixcontact.com/us/products/2792060>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2792060>



**UL Recognized**

Approval ID: E240868

# UEGM/H-FE - Intermediate element



2792060

<https://www.phoenixcontact.com/us/products/2792060>

## Classifications

### ECLASS

ECLASS-13.0	27190604
ECLASS-15.0	27190604

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEGM/H-FE - Intermediate element



2792060

<https://www.phoenixcontact.com/us/products/2792060>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.069 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)