

# UEGM 22,5 BK OHNE LOGO - Electronics housing



2792882

<https://www.phoenixcontact.com/us/products/2792882>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic housing, for PCB insertion, fully equipped with 3 screw or 6 tab connections per side

## Commercial data

Item number	2792882
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AC11
Product key	ACHCCB
GTIN	4017918243050
Weight per piece (including packing)	52.33 g
Weight per piece (excluding packing)	46.33 g
Customs tariff number	85369010
Country of origin	DE

2792882


<https://www.phoenixcontact.com/us/products/2792882>

## Technical data

### Product properties

Housing type	Component housing
Type	Connection system integrated, housing closed
Number of positions	6

### Dimensions

Dimensional drawing	
Width	22.5 mm
Length	79 mm

### Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V2
Housing material	PA 6.6


### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

## Drawings

Dimensional drawing




# UEGM 22,5 BK OHNE LOGO - Electronics housing

2792882

<https://www.phoenixcontact.com/us/products/2792882>



Dimensional drawing



UEGM 22,5... with 1 PCB, 6 positions or 12 positions (FS/FS)

Dimensional drawing




# UEGM 22,5 BK OHNE LOGO - Electronics housing


2792882

<https://www.phoenixcontact.com/us/products/2792882>

Exploded view



Schematic diagram



# UEGM 22,5 BK OHNE LOGO - Electronics housing



2792882

<https://www.phoenixcontact.com/us/products/2792882>

## Classifications

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

2792882

<https://www.phoenixcontact.com/us/products/2792882>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)