

# UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery for UPS-CP-BAT... energy storage



## Commercial data

Item number	2800427
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMURV9
GTIN	4046356551243
Weight per piece (including packing)	52,000 g
Weight per piece (excluding packing)	52,000 g
Country of origin	CN

# UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

## Technical data

### Energy storage

Battery voltage	12 V DC (per battery)
Charging voltage	271.5 V DC ... 272.5 V DC
IQ technology	no

### Product properties

Product type	Battery
IQ technology	no

### Dimensions

Width	65.00 mm
Height	95.00 mm
Depth	600.00 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 45 °C

# UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

## Classifications

### UNSPSC

UNSPSC 21.0	26111710
-------------	----------

# UPS-BAT-KIT-20X7AH - Uninterruptible power supply replacement battery



2800427

<https://www.phoenixcontact.com/us/products/2800427>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### China RoHS

Environment friendly use period (EFUP)	EFUP-3 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)