

UEGM-MSTB SO11 - Electronics housing



2786607

<https://www.phoenixcontact.com/us/products/2786607>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a green version

Electronics housing, color: green ,DIN rail housing, without vents, Complete housing, cross connection: Not provided for, width: 25 mm

Commercial data

Item number	2786607
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC11
Product key	ACHCCC
GTIN	4017918236625
Weight per piece (including packing)	48.12 g
Weight per piece (excluding packing)	48.12 g
Customs tariff number	85369010
Country of origin	DE

2786607

<https://www.phoenixcontact.com/us/products/2786607>

Technical data

Product properties

Product type	Complete housing
Housing type	DIN rail housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM-MSTB
Type	Connection system integrated, housing closed
Ventilation openings present	no

Dimensions

Width	25 mm
-------	-------

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

UEGM-MSTB SO11 - Electronics housing



2786607

<https://www.phoenixcontact.com/us/products/2786607>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2786607>



UL Recognized

Approval ID: E240868

2786607

<https://www.phoenixcontact.com/us/products/2786607>

Classifications

ECLASS

ECLASS-13.0	27190301
ECLASS-15.0	27190301

ETIM

ETIM 10.0	EC001031
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

2786607

<https://www.phoenixcontact.com/us/products/2786607>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.2 kg CO2e
---------	-------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com