

# TT-UKK5-T-BE - Surge protection base-element

2788401

<https://www.phoenixcontact.com/us/products/2788401>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

TERMITRAB base element with universal foot, with screw connections on both sides.



## Commercial data

Item number	2788401
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	CL02
Product key	CL2228
GTIN	4017918071523
Weight per piece (including packing)	24.8 g
Weight per piece (excluding packing)	0.25 g
Customs tariff number	85363010
Country of origin	GR

# TT-UKK5-T-BE - Surge protection base-element



2788401

<https://www.phoenixcontact.com/us/products/2788401>

## Technical data

### Product properties

Product type	Base element
Type	Base element, DIN rail mounting
Number of positions	1
Surge protection fault message	none
Wire pairs per module	1

### Electrical properties

Nominal current $I_N$	26 A
-----------------------	------

### Connection data

Stripping length	8 mm
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Dimensions

Width	6.2 mm
Height	87.5 mm

### Material specifications

Flammability rating according to UL 94	V-2
Housing material	PA

### Mechanical properties

#### Mechanical data

Open side panel	No
-----------------	----

### Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

# TT-UKK5-T-BE - Surge protection base-element


2788401

<https://www.phoenixcontact.com/us/products/2788401>



## Drawings

Circuit diagram



# TT-UKK5-T-BE - Surge protection base-element



2788401

<https://www.phoenixcontact.com/us/products/2788401>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)