

# SVP 2E- 48AC - Gas discharge tube



2788919

<https://www.phoenixcontact.com/us/products/2788919>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

2-electrode gas-filled surge arrester the design H, nominal voltage: 48 V AC



## Commercial data

Item number	2788919
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	NULL
Product key	CL321Z
GTIN	4017918071974
Weight per piece (including packing)	2.53 g
Weight per piece (excluding packing)	1.5 g
Customs tariff number	85389099
Country of origin	DE

# SVP 2E- 48AC - Gas discharge tube



2788919

<https://www.phoenixcontact.com/us/products/2788919>

## Technical data

### Product properties

Product type	Gas-filled surge arrester
Product family	COMTRAB
Surge protection fault message	none

### Electrical properties

Nominal voltage $U_N$	48 V AC
-----------------------	---------

### Dimensions

Width	8 mm
Height	8 mm
Depth	6 mm

### Material specifications

Color	gentian blue (RAL 5010)
	silver-colored

### Mechanical properties

#### Mechanical data

Open side panel	No
-----------------	----

### Protective circuit

Direction of action	Line-Earth Ground
Nominal voltage $U_N$	48 V AC
Output voltage limitation at 1 kV/ $\mu$ s (line-earth) spike	$\leq 600$ V
Surge protection fault message	none

# SVP 2E- 48AC - Gas discharge tube



2788919

<https://www.phoenixcontact.com/us/products/2788919>

## Classifications

### ECLASS

ECLASS-13.0	27171592
ECLASS-15.0	27171592

### ETIM

ETIM 10.0	EC002497
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# SVP 2E- 48AC - Gas discharge tube



2788919

<https://www.phoenixcontact.com/us/products/2788919>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)