

# UEGM-SE 5 BU OHNE LOGO - Housing half shell



2791249

<https://www.phoenixcontact.com/us/products/2791249>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element for electronic housing UEGM ...

## Commercial data

Item number	2791249
Packing unit	20 pc
Minimum order quantity	1 pc
Product key	ACHCCB
GTIN	4017918274467
Weight per piece (including packing)	18.507 g
Weight per piece (excluding packing)	18 g
Country of origin	DE

# UEGM-SE 5 BU OHNE LOGO - Housing half shell



2791249

<https://www.phoenixcontact.com/us/products/2791249>

## Technical data

### Product properties

Product type	Housing half shells
Housing type	Component housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM
Ventilation openings present	yes

### Material specifications

Color (Housing)	blue (RAL 5015)
Material	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

### Mounting

Mounting type	Snap in
---------------	---------

# UEGM-SE 5 BU OHNE LOGO - Housing half shell



2791249

<https://www.phoenixcontact.com/us/products/2791249>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2791249>



**UL Recognized**

Approval ID: E240868

# UEGM-SE 5 BU OHNE LOGO - Housing half shell



2791249

<https://www.phoenixcontact.com/us/products/2791249>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEGM-SE 5 BU OHNE LOGO - Housing half shell



2791249

<https://www.phoenixcontact.com/us/products/2791249>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)