

UEGM-SE 2,5 - Housing half shell



2792044

<https://www.phoenixcontact.com/us/products/2792044>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element for electronic housing UEGM ...

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2792044 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC22 |
| Product key | ACHCCB |
| GTIN | 4017918365370 |
| Weight per piece (including packing) | 16.32 g |
| Weight per piece (excluding packing) | 16.32 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

UEGM-SE 2,5 - Housing half shell



2792044

<https://www.phoenixcontact.com/us/products/2792044>

Technical data

Product properties

| | |
|------------------------------|---------------------|
| Product type | Housing half shells |
| Housing type | Component housing |
| Housing type | Basic housing |
| Housing series | UEGM |
| Product family | UEGM |
| Ventilation openings present | yes |

Material specifications

| | |
|--|------------------|
| Color (Housing) | green (RAL 6021) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

UEGM-SE 2,5 - Housing half shell



2792044

<https://www.phoenixcontact.com/us/products/2792044>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2792044>



UL Recognized

Approval ID: E240868

UEGM-SE 2,5 - Housing half shell



2792044

<https://www.phoenixcontact.com/us/products/2792044>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UEGM-SE 2,5 - Housing half shell



2792044

<https://www.phoenixcontact.com/us/products/2792044>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.069 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com