

UEGM/H-FE BU - Intermediate element



2792497

<https://www.phoenixcontact.com/us/products/2792497>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic housing, Intermediate element with base latch, without vents, width: 27.3 mm, height: 79.2 mm, depth: 66.3 mm, color: blue (similar RAL 5015), cross connection: Not provided for

Commercial data

Item number	2792497
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHCCB
GTIN	4017918342128
Weight per piece (including packing)	14.52 g
Weight per piece (excluding packing)	10.66 g
Country of origin	DE

2792497

<https://www.phoenixcontact.com/us/products/2792497>

Technical data

Product properties

Product type	Component housing center part
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM
Ventilation openings present	no

Dimensions

Width	27.3 mm
Height	79.2 mm
Depth	66.3 mm

Material specifications

Color (Housing)	blue (RAL 5015)
Material Housing	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Latching with housing half-shell
---------------	----------------------------------

UEGM/H-FE BU - Intermediate element



2792497

<https://www.phoenixcontact.com/us/products/2792497>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2792497>



UL Recognized

Approval ID: E240868

UEGM/H-FE BU - Intermediate element



2792497

<https://www.phoenixcontact.com/us/products/2792497>

Classifications

ECLASS

ECLASS-13.0	27190604
ECLASS-15.0	27190604

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UEGM/H-FE BU - Intermediate element



2792497

<https://www.phoenixcontact.com/us/products/2792497>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.106 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com