

# FL SWT - Network management software



2831044

<https://www.phoenixcontact.com/us/products/2831044>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Factory Manager, multilingual, configuration and diagnostics software for Ethernet networks in automation

## Your advantages

- Integrated trap receiver
- Integrated TFTP and BootP server

## Commercial data

Item number	2831044
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNN155
GTIN	4017918599331
Weight per piece (including packing)	236 g
Weight per piece (excluding packing)	236 g
Customs tariff number	85234945
Country of origin	DE

## Technical data

### Product properties

Product type	Network management software
Scope of supply	CD-ROM with multilingual product version, online documentation -Internet Explorer, Service Pack and Acrobat Reader (D/E) - Winsock 2 -Java Runtime Environment

### System properties

Intended use for the software	Configuration
	Diagnostics

### Functionality

Basic functions	The Factory Manager is a software tool designed for the requirements of the industrial user, for startup, operation and maintenance of Ethernet networks in the automation environment.
Configuration	Allocation of IP addresses (via integrated BootP server), support for SNMPv1 (network management), detecting devices in the network (autodiscovery), exporting network configurations as doc, xls or txt file, firmware update via integrated TFTP server
Diagnostics	Status monitoring of devices, detailed representation of information on the devices (e.g. IP address, MAC address, network status), alarm and event logging (e.g. SNMP traps, BootP messages, network scanner, messages can be exported as doc, .xls, .txt files
Web-based management	Access via integrated browser
Associated hardware	Ethernet infrastructure components

### System requirements

Operating equipment	Keyboard, mouse recommended
Operating system	Windows 2000, Windows NT, Windows XP, TCP/IP Stack, SNMP Agent
Processor	PC Pentium > 266 MHz
Hard disk memory	min. 20 Mbyte (For Factory Manager)
Network card	Correctly configured ETHERNET network card with TCP/IP protocol stack
Supported browsers	Internet Explorer 4.01 or higher
Languages supported	German, English
Optical drive	CD-ROM
Software requirements	Internet Explorer 4.x or higher
	TCP/IP stack, SNMP services
	Only with Windows 95: Winsock 2 update
	Windows 9x, Window NT, Windows 2000, Windows XP (Sp1 required)
Screen resolution	640 x 480

2831044

<https://www.phoenixcontact.com/us/products/2831044>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)